

ALD for advanced lithionic devices: Hybrid ultrathin Solid-State Electrolytes

Ilyass Ghandari, Nicolas Gauthier, Sylvain Poulet, Mikhael Bechelany, Messaoud Bedjaoui

▶ To cite this version:

Ilyass Ghandari, Nicolas Gauthier, Sylvain Poulet, Mikhael Bechelany, Messaoud Bedjaoui. ALD for advanced lithionic devices: Hybrid ultrathin Solid-State Electrolytes. AVS ALD/ALE 2024, AVS, Aug 2024, HELSINKI, Finland. cea-04679132

HAL Id: cea-04679132 https://cea.hal.science/cea-04679132v1

Submitted on 27 Aug 2024

HAL is a multi-disciplinary open access archive for the deposit and dissemination of scientific research documents, whether they are published or not. The documents may come from teaching and research institutions in France or abroad, or from public or private research centers.

L'archive ouverte pluridisciplinaire **HAL**, est destinée au dépôt et à la diffusion de documents scientifiques de niveau recherche, publiés ou non, émanant des établissements d'enseignement et de recherche français ou étrangers, des laboratoires publics ou privés.

ALD for advanced lithionic devices: Hybrid ultrathin Solid-State Electrolytes.

<u>Ilyass GHANDARI</u>, Nicolas GAUTHIER¹, Sylvain POULET¹, Mikhael BECHELANY², Messaoud BEDJAOUI¹

¹ CEA Leti, 38000 Grenoble, France ² IEM UMR 5635, CNRS, 34090, Montpellier, France ilyass.qhandari@cea.fr

Innovative micro-supercapacitors (MSCs) such as LiPON based MSCs are emerging to address the technological challenges faced at higher frequencies (>kHz),especially energy harvesting and storage, which requires efficient materials coupled with improved microfabrication techniques to unlock the full potential of such devices. In this way, conformal and self-limiting surface reactions enabled by Atomic Layer Deposition (ALD) give great advantages to form and optimize Lithium based thin films compatible with complex geometries. Here in, a multidisciplinary approach was conducted to develop the thermal ALD process, characterize the physico-chemical properties and evaluate the electrical performances of nano-hybrid Solid State Electrolytes (SSE).

The thermal ALD process for ultrathin LiPON films (<25nm) is realized using Li-Bistrimethylsilylamide (LiHMDS) and Diethylphosphoramidate (DEPA) precursors in a deposition temperature range 300-350°C. To further optimize LiPON's electrochemical performances, Trimethyl Aluminium (TMA) and H₂O were pulsed to incorporate Al₂O₃ in SSE films. Ellipsometry was used to calibrate the growth rate of LiPON-based films. The microstructure was analyzed by X-Ray Diffraction (XRD) to highlight the amorphous nature of the thin films, indicating that the Al₂O₃ incorporation preserves favorable amorphous structure, which is a key characteristic for achieving excellent electrochemical performances [1]. The XPS spectra show typical core peaks (Li_{1s}, P_{2D}, O_{1s}, N_{1s}, Al_{2D}) corresponding to different LiPON based samples. The analysis reveals that Al₂O₃ insertion seems to impact the nitrogen environment. From NIs spectra (Fig.1), the peaks present two main components located at 397 eV and 399 eV, attributed respectively to a divalent nitrogen state (N_d) and a trivalent nitrogen state (N_t) [1], whose proportion evolves as a function of Al₂O₃ incorporation. Thus, the concentration of divalent nitrogen becomes predominant over trivalent nitrogen, inducing an increase in the N_d/N_t fraction when more Al₂O₃ is introduced. This variation has frequently been reported as a major factor in improving Li-ion mobility [1]. The Electrochemical Impedance Spectroscopy (Fig.2) addresses the changes in Li-ion conductivity of the LiPON films upon addition of Al₂O₃ concentration.

This work provides a solid ALD approach with promising potential to optimize the electrical performances (ie Li⁺mobility, areal capacitance etc) in ultrathin SSE, shedding light on the application of such hybrid microstructures in several Lithionic devices such as microsupercapacitors, micro-batteries and transistors.

Supporting Information

ALD for advanced lithionic devices: Hybrid ultrathin Solid-State Electrolytes.

<u>Ilyass GHANDARI</u>, Nicolas GAUTHIER¹, Sylvain POULET¹, Mikhael BECHELANY², Messaoud BEDJAOUI¹

CEA Leti, 38000 Grenoble, France

ilyass.ghandari@cea.fr




Fig 1: Typical core peaks (Li1s, P2p, O1s and N1s) corresponding to two different LiPON samples: LiPON (reference) and LiPON Al₂O₃ (0,1%)




Fig 2: Nyquist plots of electrochemical impedance spectroscopy (EIS) of two samples tested: LiPON (reference) and LiPON $Al_2O_3(0,1\%)$, for a frequency range of 1Hz - 1MHz, in a MIM structure Ti/LiPON/TiN.